



Pre-Fabricated Assemblies

Improve onsite productivity
 Greater dimensional stability
 Take rebar tying off the critical path



Mast Arm Length	1 Foundation Depth	2 Foundation Sonotube Diameter	3 Spiral Diameter	4 Quantity of Rebars	5 Size of Rebars	6 Order Number	7 Cage Description
Less than 30'	10'-0"	30	24	8	6	153-4SP24-8696	#4 SPIRAL 24D 6" P 3-TURNS T&B ON 8#6(V)9'-6"
Greater than or equal to 30' and less than 40'	13'-6"	30	24	8	6	153-4SP24-86130	#4 SPIRAL 24D 6" P 3-TURNS T&B ON 8#6(V)13'-0"
	11'-0"	36	30	12	7	153-4SP30-127106	#4 SPIRAL 30D 6" P 3-TURNS T&B ON 12#7(V) 10'-6"
Greater than or equal to 40' and less than 50'	13'-0"	36	30	12	7	153-4SP30-127126	#4 SPIRAL 30D 6" P 3-TURNS T&B ON 12#7(V) 12'-6"
Greater than or equal to 50' and up to 55'	15'-0"	36	30	12	7	153-4SP30-127146	#4 SPIRAL 30D 6" P 3-TURNS T&B ON 12#7(V)14'-6"
Greater than 56' and up to 65'	21'-0"	42	36	16	8	153-4SP36-168206	#4 SPIRAL 36D6" P 3-TURNS T&B ON 16#8(V)20'-6"
Greater than or equal to 65' and up to 75'	25'-0"	42	36	16	8	153-4SP36-168246	#4 SPIRAL 36D6" P 3-TURNS T&B ON 16#8(V)24'-6"



ready to tip-in-place

Our welding is compliant with AWS D1.4 using weldable A706 rebar. IDOT 878-001 STD Mill Certs provided



call Jim Owens 630-209-4888
 Owens Supply Company
 10025 Clow Creek Dr. Plainfield, IL. 60585-7531
 P:1.630.596.9999 F:1.630.596.9995
 email:sales@owensupply.com